HY	Product Information		
HYYON [®] INDUSTRIAL	SILICAGEL blue, granules		
Date: 01 / 2019	PI-No.: SG-11	page 1 of 2	
Revision: 10	11-110 30-11		
Product Description	Silica gel, blue irregular shaped gr an internal surface area of app of its very large surface area, adsorption for water vapo moisture, turns from blue indicating the relative hun environments. The internal uniform, the physical and cl stable, the thermal stability mechanical strength is high.	prox. 800m ² /g. Because , SG-11 exhibits a high pur. ,when absorbing to light red, visually midity of the given micropore structure is hemical properties are	
	p (11 Q) (supthetic amorphous c	ilicium diovido)	
Formula SiO	2. n (H ₂ O) (synthetic amorphous s	ilicium dioxide)	
CAS-No. 763	1-86-9		
Physical and chemical Adsorption capacity and color			
,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,			
	RH=50% ≥20.0% purple		
Characteristics	RH=90% ≧28.0 light red		
	Moisture loss (140 °C 4h)	Max. 5%	
	Bulk density	650 — 80 0 g/l	
	oun denotey	000 000 0/1	

HYYON INDUSTRIL

HY	Product Information			
HYYON [@] INDUSTRIAL	SILICAGEL blue,	granules		
Date: 01 / 2019 Revision: 10	PI-No.: SG-11	page 2 of 2		
		·		
Grain size				
2 – 5 mm				
Other special gradings on request				
	Due to its special pore structure SG-11 is applied for many technical processes: Mainly used for absorbing moisture, anti-rusting of instruments, gauges and equipment in the enclosed conditions. After absorbing moisture, it turns from blue to red, visually indicating the relative humidity of the given environments. When being used with ordinary silica gel or drier, it indicates to which extent the drier absorbs the moisture and judges the relative humidity of a given environment. It is widely used as silica gel drier for the packing of precision instruments, leathers, electric appliances, etc. Selective adsorption separation of organic gas or liquid. The temperature at reactivation should not exceed 180 °C.			
Packing	Airtight in 25 kg cartons,bags w 500 kg bulk bags with PE-Inliner.	vith PE-Inliner,Airtight in		
Handling	SG-10must always be kept in airt pre-adsorption with water vapo be used at continual exposure to	our. Face masks should		
Note	Any details of application possibilities do not the obligation of performing his own tests the seller, in order to determine their rocesses and purposes. Application, use a cannot be controlled by the seller and are the purchaser.	s on the material supplied by suitability for the intended nd processing of the material		

HYYON INDUSTRIL